


The B6 XL is supplied with either bottom or side mounted captive M8 fittings. To fit TR1 or TR3 Tillett adjustment runners to the base mounted version, you will need the TK5 fitting kit as the runners have to be spaced away from the lower seat surface. The side mount version can use brackets PTBi, PTBO, TBFIA, STBi, STBO, and Elise brackets EBR, EBR 17+, EBS, EBP. These brackets have a 2° from vertical angle, which matches the side of the seat. Brackets which do not match this angle will unduly stress the composite.

For the 8855-1999 homologated FIA version order the B6 XL Screamer.

## B6 XL Dimensions



**B6-47 XL Carbon GRP  
Side Mount**



43 cm wide with rolled edge cut off, or 47 cm edges on external dim.



38 cm external across the base moulding 39 cm across bolting points if you have the side mount version

